


# Rittal – The System.

Faster – better – everywhere.



## AS 4055.720

# Elektrohydraulické čerpadlo

State: 30.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.720 - Elektrohydraulické čerpadlo

The electro-hydraulic pump is used to drive products in the CW 120-S series.



## Features

Obj. č.	AS 4055.720
Menovitý príkon	1,3 kW
Filling volume	3,2 l
Working volume	2,2 l
Flow rate (max.)	1,1 l/min
Oil (type)	HLP 46
Menovité prevádzkové napätie	230 V, 50 Hz
Menovitý prúd	5,65 A
Rozmery stroja	Šírka: 400 mm Výška: 325 mm Hĺbka: 335 mm
Využitelná plocha	Šírka: 402 mm Výška: 342 mm Hĺbka: 397 mm
Prípustný prevádzkový tlak (p max.)	700 bar
Balenie	1 pc(s).
Netto hmotnosť	32 kg
Brutto hmotnosť	34,5 kg
Číslo colnej sadzby	84138100

## Features

---

ETIM 9	EC011047
ETIM 8	EC011047
ECLASS 8.0	27301290
Popis výrobku	Elektrohydraulické čerpadlo vhodné pre CW 120-S a hydraulický valec

## Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------