


Rittal – The System.

Faster – better – everywhere.



SZ 4540.500

Kombinované uholníky

State: 26.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4540.500 - Kombinované uholníky pre VX, TS

For optimum distribution of tensile forces during transportation of bayed enclosures by crane.



Features

Obj. č.	SZ 4540.500
Materiál	Nerezová oceľ 1.4301 (AISI 304)
Rozsah dodávky	Vrátane upevňovacieho materiálu
Vhodné pre	Typ skrine: VX TS
Type rating podľa UL 50E	Type 1 Type 12
Protection category NEMA	NEMA 1, 12
Stupeň krytia IP podľa normy IEC 60 529	IP 55
Balenie	2 pc(s).
Netto hmotnosť	1,2 kg
Brutto hmotnosť	1,4 kg
PCF per pack (cradle-to-gate)	5,3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73182900
ETIM 9	EC002622
ETIM 8	EC002622

Features

ECLASS 8.0

27189234

Popis výrobku

Kombinovaný uholník SZ nerez

Approvals

Approvals

UL + C-UL - FTTA