

Rittal – The System.

Faster – better – everywhere.



TS 4579.000 Montážna výstuha

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4579.000 - Montážna výstuha pre VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Obj. č.	TS 4579.000
Technické údaje	Dierovanie Ø 4,5 mm v rozmerovom rastri 25 mm
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho materiálu
Dĺžka	790 mm
Vhodné pre šírku dverí	900 mm
Možnosti montáže VX SE	Do šírky dverí 900 mm V skrini šírky 800 mm, na vnútornej montážnej rovine
Možnosti montáže AX	V skrini šírky 800 mm, v kombinácii s lištami pre vnútorné vybavenie AX a podlahovou montážnou lištou AX
Možnosti inštalácie AX z nehrdzavejúcej ocele	V šírke rozvádzača 800 mm Pri šírke dverí 800 mm, v spojení s dierovanou lištou dverí
Možnosti montáže TS	V skrini šírky/hĺbky 800 mm, na vnútornej montážnej rovine
Možnosti montáže TP	V podstavci pultu TP a kompaktného pultu, šírka rozvádzača 800 mm, v spojení s lištou pre vnútornú montáž pre TP, kompaktná rozvážacia skriňa HD

Features

Vhodné pre	Typ skrine: TS VX SE TP AX Šírka/hĺbka: 800 mm
Balenie	20 pc(s).
Netto hmotnosť	8 kg
Brutto hmotnosť	8,1 kg
PCF per pack (cradle-to-gate)	37,23 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Popis výrobku	Montážna lišta TS, pre TS, VX SE, TP, pre vnútornú montážnu rovinu: pre š/h: 800 mm, pre šírku dverí: 900 mm, D: 790 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------