

Rittal – The System.

Faster – better – everywhere.



TS 4594.000

Montážna výstuha

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4594.000 - Montážna výstuha pre VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Obj. č.	TS 4594.000
Technické údaje	Dierovanie Ø 4,5 mm v rozmerovom rastri 25 mm
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho materiálu
Dĺžka	290 mm
Vhodné pre šírku dverí	400 mm
Možnosti montáže VX SE	Do šírky dverí 400 mm
Možnosti montáže AX	V skrini šírky 300 mm a výšky skrine 400 mm, v spojení s lištou pre vnútornú montáž AX
Možnosti inštalácie AX z nehrdzavejúcej ocele	V šírke rozvádzača 300 mm
Možnosti montáže AX z plastu	Do šírky dverí 400 mm
Možnosti inštalácie 3-dielnej skrine AX	Hĺbka skrine 473 mm
Možnosti montáže TS	Do šírky dverí 400 mm
Installation options for VX base/plinth, stainless steel	In base/plinth depth 400 mm, in conjunction with M6 multi-tooth screws and M6 nuts

Features

Vhodné pre	Typ skrine: VX TS VX SE AX AX plastic AX wall-mounted enclosure, 3-part
Vhodné pre	Podstavcový systém VX, nehrdzavejúca oceľ
Balenie	20 pc(s).
Netto hmotnosť	2,94 kg
Brutto hmotnosť	3,02 kg
PCF per pack (cradle-to-gate)	14,05 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Popis výrobku	TS montážna lišta, pre TS, VX SE, TP, pre šírku dverí: 400 mm, D: 290 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------