

Rittal – The System.

Faster – better – everywhere.



SZ 4944.000

Profilové lišty tvaru C 30/15

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4944.000 - Profilové lišty tvaru C 30/15 podľa normy EN 60 715 pre VX, TS, VX SE

For direct external mounting on the horizontal enclosure section or vertical enclosure section with additional assembly components.



Features

Obj. č.	SZ 4944.000
Materiál	Oceľový plech
Povrch	Pozinkovaný
Dĺžka	555 mm
Možnosti montáže	Na vnútornej montážnej rovine na profile skrine VX Na vertikálnom profile skrine TS, VX SE pomocou fixačnej matice TS 8800.808 alebo adaptérovej lišty zaisťujúcej kompatibilitu s VX Na vodorovný profil skrine VX SE dole a hore na šírku Na horizontálnom profile skrine VX SE na hĺbku dole (bez montážnej dosky) a hore cez fixačnú maticu 8800.808 Na horizontálnom profile skrine TS V šírke alebo hĺbke 3-dielnej skrine AX. V závislosti od montáže sa musí lišta skrátiť na požadovanú dĺžku.
VX base/plinth installation options	In base/plinth width 600 mm on the base/plinth trim panels, in conjunction with holder/spacer
AX base/plinth installation options	In base/plinth width 600 mm, in conjunction with metal multi-tooth screws

Features

Vhodné pre	Typ skrine: VX TS AX wall-mounted enclosure, 3-part Šírka/hĺbka: 600 mm
Vhodné pre	System podstavca AX System podstavca VX
Balenie	6 pc(s).
Netto hmotnosť	2,118 kg
Brutto hmotnosť	2,4 kg
PCF per pack (cradle-to-gate)	11,12 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC000386
ETIM 8	EC000386
ECLASS 8.0	27400602
Popis výrobku	SZ C profilová lišta 30/15 podľa EN 60 715, pre TS, SE, pre š/h: 600 mm, d: 555 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------