


Rittal – The System.

Faster – better – everywhere.



VX 5301.518 Modul koliesok

State: 8.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.518 - Modul koliesok pre VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

Features

Obj. č.	VX 5301.518
Rozsah dodávky	1 prepravny modul s 2 otočnými kolieskami 1 prepravny modul s 2 pevnými kolieskami Vrátane upevňovacieho materiálu
Rozmery	Šírka: 756 mm Výška: 82,5 mm Hĺbka: 79 mm
Montážny pokyn	Podlahová oblasť musí byť pri montážnych bodoch otvorená
Vhodné pre	Typ skrine: VX: = 800 mm Typ skrine: VX IT
Zaťažiteľnosť	Max. povolená záťaž: statická 15 000 N Max. povolená záťaž: dynamická 10 000 N
Poznámka	Maximálne prípustná nosnosť (dynamická) vo výške 10 000 N sa vzťahuje na prepravu na kolieskach po rovnom teréne.
Balenie	1 pc(s).
Netto hmotnosť	11,5 kg
Brutto hmotnosť	12,12 kg
Číslo colnej sadzby	94039910
ETIM 9	EC002621
ECLASS 8.0	27189262
Popis výrobku	Modul koliesok pre VX IT, pre šírku: 800 mm, pre ľahký pohyb na mieste, možno namontovať priamo na skriňu.