

Rittal – The System.

Faster – better – everywhere.



DK 5301.602

Dvere z ocelového plechu, zvisle delené, uzavreté

State: 28.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5301.602 - Dvere z ocelového plechu, zvisle delené, uzavreté pre VX IT

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.



Features

Obj. č.	DK 5301.602
Materiál	Ocelový plech
Povrch	S nástrekom
Farba	RAL 7035 Komfortná rukoväť VX, pánty: RAL 9005
Rozsah dodávky	Dvere, vertikálne delené, s komfortnou rukoväťou VX pre profilovú cylindrickú polvložku s bezpečnostným zámkom 3524 E, vpravo 3 pánty 180°, namontované na každej polovici dverí Vrátane upevňovacieho materiálu
Montážny pokyn	Pre uhol otvorenia dverí 180° pri radovom spojení je potrebný 180° pánt pre radové spojení
Poznámka	Uhol otvorenia dverí pri samostatnej inštalácii max. 240° Uhol otvorenia dverí pri radovom spojení max. 160°

Features

Stupeň krytia IP podľa normy IEC 60 529	IP 20
Vhodné pre	Typ skrine: VX IT Šírka: = 600 mm Výška: = 2.000 mm
Balenie	1 pc(s).
Netto hmotnosť	36 kg
Brutto hmotnosť	41 kg
Číslo colnej sadzby	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
Popis výrobku	Dvere z oceleového plechu, vertikálne delené, plné pre VX IT, pre šírku skrine: 600 mm, pre výšku skrine: 2 000 mm, oceleový plech, lakované, RAL 7035, rukoväť a pánty: RAL 9005