

Rittal – The System.

Faster – better – everywhere.



VX 5302.030

Klzná lišta, 2 U, pevná montáž, s veľkou nosnosťou

State: 21.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.030 - Klzná lišta, 2 U, pevná montáž, s veľkou nosnosťou pre VX IT

For mounting between a front and rear pair of mounting angles for 482.6 mm (19") standard mounting angles and 482.6 mm (19") dynamic mounting angles in the VX IT.



Features

Obj. č.	VX 5302.030
Výhody	Jednoduché zavesenie do systémového dierovania 19" montážnych profilov po nastavení potrebných vzdialeností 19" roviny
Oblasti použitia	Na upevnenie medzi prednú a zadnú 19" montážnu rovinu Na podoprenie ťažkých vstavaných komponentov
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho materiálu
Zaťažiteľnosť	2000 N, statické
Poznámka	Efektívna kontaktná plocha na každej strane 35 mm
Možnosti montáže	pre 19" štandardnú profilovú lištu: vzdialenosť medzi rovinami 320/345 mm pre 19" profilovú lištu dynamic: vzdialenosť medzi rovinami 300/325 mm
Balenie	2 pc(s).
Netto hmotnosť	1,04 kg
Brutto hmotnosť	1,04 kg

Features

Číslo colnej sadzby	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Popis výrobku	Klzná lišta, 2 U, pevná montáž, pre vysoké zaťaženie, pre VX IT, pre montáž na prednú montážnu rovinu, na podporu ťažkých inštalácií, efektívna kontaktná plocha na každej strane 35 mm