

# Rittal – The System.

Faster – better – everywhere.



## VX 5302.110 Montážne uholníky

State: 1.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5302.110 - Montážne uholníky pre VX IT 19" profilové lišty

Mounting bracket for mounting 482.6 mm (19") mounting angles in VX IT network/server racks.

## Features

Obj. č.	VX 5302.110
Prevedenie	pre 19" profilovú lištu VX IT štandard
Výhody	Vyrovnanie potenciálu profilových lišt prebieha priamo cez upevnenie
Materiál	Oceľový plech
Povrch	S nástrekom
Farba	RAL 9005
Rozsah dodávky	Vrátane upevňovacieho materiálu
Vhodné pre	Šírka: = 600 mm
Balenie	4 pc(s).
Netto hmotnosť	0,6 kg
Brutto hmotnosť	0,62 kg
PCF per pack (cradle-to-gate)	2,4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73182900
ETIM 9	EC002620
ECLASS 8.0	27189261
Popis výrobku	Montážny uholník pre VX IT 19" profilové lišty, pre uchytenie palcových profilových lišt, štandard, do VX IT dátových/serverových skríň. Pri rozvádzačoch so šírkou 600 mm sa uchytenie vykonáva priamo na rámovú konštrukciu

# Approvals

---

Explanations

Manufacturer's declaration