

Rittal – The System.

Faster – better – everywhere.



VX 5302.166 Híbkové vzpery

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.166 - Híbkové vzpery pre profilové lišty 482,6 mm (19")

L-shaped mounting angles, also for accommodating server system installation kits.

Features

Obj. č.	VX 5302.166
Prevedenie	pre 19" profilovú lištu VX IT štandard pre 19" profilovú lištu VX IT dynamic
Výhody	Obzvlášť vysoký príkon až 15000 N Zvýšená stabilita vďaka vylepšenému rozdeleniu záťaže Montáž môže byť symetrická alebo asymetrická Viac miesta pre vedenie káblov alebo integráciu Liquid Cooling Unit (LCU) pri jednostrannej, asymetrickej (bočne presadenej) inštalácii Optimálne pre integráciu 19-palcových profilových lišt pre alternatívne vybavenie 21", 23" alebo 24" komponenty
Materiál	Oceľový plech
Povrch	S nástrekom
Farba	RAL 9005
Rozsah dodávky	Híbkové vzpery Vrátane upevňovacieho materiálu
Montážny pokyn	Na upevnenie profilových lišt v skrinách s hĺbkou >1000 mm a šírkou > 600 mm sú navyše potrebné nosné lišty pre VX IT
Vhodné pre	Typ skrine: VX IT, štandard VX IT, dynamic Šírka: = 600 mm Hĺbka: = 1.200 mm
Balenie	2 pc(s).
Netto hmotnosť	3,5 kg
Brutto hmotnosť	3,652 kg
PCF per pack (cradle-to-gate)	27,1 kg CO2 eq (Cat B)

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Popis výrobku	Hĺbková vzpera pre profilové lišty 482,6 mm (19"), na uchytenie palcových profilových lišt. Pre šírku skrine: = 600 mm, pre hĺbku skrine: = 1 200 mm, oceľový plech, lakovaný, RAL 9005

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------