


Rittal – The System.

Faster – better – everywhere.



DK 5302.200

Zaslepovací panel, 482,6 mm (19")

State: 8.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.200 - Zasleyovací panel, 482,6 mm (19")

Upevnenie bez náradia

Enables fast, tool-free fastening and thermal partitioning of unconfigured mounting surfaces in a 482.6 mm (19"), 1 U pitch pattern.

Features

Obj. č.	DK 5302.200
Výhody	Larger areas may be covered by combining multiple units. Versatile panel for individual requirements. Extendible on both sides with additional panels. Možnosť opakovanej montáže a použitia
Materiál	Plast Správanie pri horení podľa UL94 HB, bez obsahu halogénu
Povrch	Matt
Farba	RAL 9005
Rozsah dodávky	Zasleyovací panel, 1 U s integrovaným rýchlym upevnením
Build-up height	1 U
Rozmery	Šírka: 482,6 mm
Výškové moduly	1 U
Balenie	5 pc(s).
Netto hmotnosť	0,4 kg
Brutto hmotnosť	0,605 kg
PCF per pack (cradle-to-gate)	1,99 KG CO2e
Číslo colnej sadzby	73269098
ETIM 9	EC000456
ECLASS 8.0	27189217
Popis výrobku	Záslepka 482,6 mm (19"), 1 U, beznástrojové upevnenie, plast, RAL 9005