

**Rittal – The System.**

Faster – better – everywhere.



**DK 5501.825**

**Vzduchové deflektory pre TS IT 19"  
profilové lišty**

State: 21.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.825 - Vzduchové deflektory pre TS IT 19" profilové lišty

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

Obj. č.	DK 5501.825
Oblasti použitia	Na oddelenie chladných a teplých zón vo vnútri skrine, uzavretej uličky alebo pri použití systému LCP.
Materiál	Oceľový plech Zaslepovací panel: plast, UL 94-HB, bez obsahu halogénu Kefová lišta: plast, UL 94-HB
Povrch	S nástrekom
Farba	RAL 9005
Rozsah dodávky	2 vertikálne kryty 2 horizontálne kryty 4 kefové lišty 4 kusy celulózovej PU peny Vrátane upevňovacieho materiálu
Montážny pokyn	Vertikálne clony s kefovou lištou je možné pre oddelenie namontovať na prednej aj na zadnej 19" profilovej lišty. Montáž horizontálnych clôn s kefovými lištami je možná len na predných 19" profilových lištách.
Vhodné pre	Šírka: 600 mm Výška: 2.200 mm

# Features

Balenie	1 pc(s).
Netto hmotnosť	4,918 kg
Brutto hmotnosť	5,177 kg
Číslo colnej sadzby	73269098
ETIM 9	EC000331
ECLASS 8.0	27189272
Popis výrobku	DK Air baffle plate, WxH: 600x2200 mm, For TS IT 482.6 mm (19") mounting angles