


Rittal – The System.

Faster – better – everywhere.



SE 5831.680

Samostatne stojaca systémová skriňa VX SE

State: 31.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SE 5831.680 - Samostatne stojaca systémová skriňa VX SE IP 66/NEMA 4

Free-standing sheet steel enclosure with stable enclosure body, two integral mounting levels, screw-fastened rear panel and door. Roof and sides from a single piece with roll-formed frame. Fully compatible with the VX25 baying system. Efficiency is enhanced, as the side panels no longer need to be fitted. Increased protection with IP 66 / NEMA 4.



Features

Obj. č.	SE 5831.680
Materiál	Skriňa: ocel'ový plech 1,5 mm Dvere: ocel'ový plech, 2,0 mm Zadná stena: ocel'ový plech, 1,5 mm Podlaha: ocel'ový plech, 1,5 mm Montážna doska: ocel'ový plech, 3,0 mm
Povrch	Skrinka, dvere a zadná stena: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba Montážna doska: pozinkovaná Podlahy: základná farba nanosená máčaním a štruktúrovaná prášková farba
Farba	RAL 7035

Features

Rozsah dodávky	Skriňa hore a po stranách uzavretá Dvere Pánty dverí vpravo, je možné zameniť na ľavú stranu Montážna doska Podlaha, prírubová doska (prírubové dosky) Zadná stena s možnosťou odskrutkovania Uzáver: Doppelbart, 3 mm 2 montážne lišty 18 x 39 mm
Rozmery	Šírka: 800 mm Výška: 1.800 mm Hĺbka: 400 mm
Rozmery montážnej dosky (Š x V)	699 mm x 1.696 mm
Stupeň krytia IP podľa normy EN 60 529	IP 66
Stupeň krytia NEMA	NEMA 4
Type rating podľa UL 50E	Type 1 Type 2 Type 3 Type 3R Type 4 Type 12
Kód IK	IK10
Počet dverí	1
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	121,1 kg
Brutto hmotnosť	124,8 kg
PCF per pack (cradle-to-gate)	359,73 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC000261

Features

ECLASS 8.0	27180101
------------	----------

Popis výrobku	VX SE samostatne stojaca systémová skriňa, ŠxVxH 800x1800x400 mm, oceľový plech, IP66 / NEMA 4, s montážnou doskou, jednodverová, dvere vpredu
---------------	------------------------------------------------------------------------------------------------------------------------------------------------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Certificates	Surface finish Protection category
--------------	---------------------------------------

Explanations	Declaration of conformity Declaration of conformity UK PCF-declaration
--------------	------------------------------------------------------------------------------