

Rittal – The System.

Faster – better – everywhere.



CP 6206.460

**Adaptér na nastavenie sklonu
+100°/-60°**

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6206.460 - Adaptér na nastavenie sklonu +100°/-60° na pripojenie nosných ramien 120 x 65 mm

For mounting on IW worktop, prepared for attachment Ø 130 mm, surfaces or attachments/
couplings with support arm connection 120 x 65 mm. To fit enclosures up to 20 kg with support
arm connection. With cable tube for protected cable entry.

Features

Obj. č.	CP 6206.460
Prevedenie	Pre montáž na Pracovná doska IW, pripravená na upevnenie o Ø 130 mm Plochy Upevnenie/spojenie s pripojením nosných ramien 120 x 65 mm Vhodný pre skrinky do 20 kg s pripojením nosných ramien 90 x 71 mm Ø 130 mm 120 x 65 mm VESA Standard 75 S káblovým tunelom pre chránený priechod káblov
Materiál	Adaptér pre nastavenie sklonu: oceľový plech, s nástrekom Manžeta: plast
Farba	Adaptér na nastavenie sklonu: RAL 7035 Manžeta: RAL 7024
Rozsah dodávky	Vrátane upevňovacieho materiálu Manžeta
Otočné/s nastaviteľným sklonom	Yes
Tilt angle note	Pomocou upínacej páčky nastaviteľný v rastrí 7,2° a pomocou priloženej dorazovej skrutky vymezený na +100°/-15°
Balenie	1 pc(s).
Netto hmotnosť	0,86 kg
Brutto hmotnosť	0,871 kg
PCF per pack (cradle-to-gate)	3 kg CO2 eq (Cat B)

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC000882
ECLASS 8.0	27400556
Popis výrobku	Adaptér sklonu CP +100°/-60°, CP 60/120, pre pripojenie nosného ramena 120 x 65 mm

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------