


Rittal – The System.

Faster – better – everywhere.



CP 6538.000

Ovládacie skrinky s dverami

State: 1.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6538.000 - Ovládacie skrinky s dverami

Command panel housing with door, sheet steel, with aluminium handle strips. Door opening on the front. Protection category IP 55. Cut-out and reinforcement for CP-L support arm system, Ø 130 mm.

Features

Obj. č.	CP 6538.000
Materiál	Skriňa a dvere: ocelový plech Držadlové lišty: hliník Krytky: plast
Povrch	Skriňa a dvere: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba Držadlové lišty: s práškovým nástrekom
Farba	Skriňa a dvere: RAL 7035 Držadlové lišty a krytky: RAL 5018
Rozsah dodávky	Skriňa s výrezom a zosilnením pre systém nosných ramien CP-L, Ø 130 mm Otočný uzáver s uzatváracou vložkou Doppelbart 3 mm Dvere s tesniacim rámom Bočné držadlové lišty a krytky
Rozmery	Šírka: 400 mm Výška: 400 mm Hĺbka: 180 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55
Poznámka	Zámena pripojenia nosných ramien a pántov dverí je možná otočením skrinky
Základný materiál	Aluminium
Balenie	1 pc(s).
Netto hmotnosť	9,099 kg
Brutto hmotnosť	9,578 kg
Číslo colnej sadzby	94032080

Features

ECLASS 8.0

27180505