

Rittal – The System.

Faster – better – everywhere.



TP 6722.500

**Horné diely pultu pre 3-dielnu
montáž**

State: 8.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 6722.500 - Horné diely pultu pre 3-dielnu montáž

Four widths offer excellent pre-requisites for individual monitoring and a three-piece configuration of the TopConsole system.

Features

Obj. č.	TP 6722.500
Materiál	Skriňa: oceľový plech 1,5 mm Dvere a kryt pultu: oceľový plech 2,0 mm, po obvode polyuretánové penové tesnenie
Povrch	základná farba nanesená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skriňa Kryt s pántami umiestnenými dole, vrátane držiaka krytu Dno otvorené pre individuálne privedenie káblov
Kód IK	IK08
Základný materiál	Sheet steel
Rozmery	Šírka: 1.200 mm Výška: 720 mm Hĺbka: 240 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Balenie	1 pc(s).
Netto hmotnosť	33,25 kg
Brutto hmotnosť	35 kg
Číslo colnej sadzby	94032080
ETIM 9	EC000784
ECLASS 8.0	27180504

Features

Popis výrobku	Systém TP TopConsult, horná časť pultu pre 3-dielnu štruktúru, ŠxH: 1200x720 mm, oceľový plech
---------------	---

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK