


Rittal – The System.

Faster – better – everywhere.



IW 6900.700

Priemyselné pracovné stanice

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IW 6900.700 - Priemyselné pracovné stanice

Lower enclosure section, based on VX SE for Industrial Workstations.



Features

Obj. č.	IW 6900.700
Prevedenie	Dizajnové dvere, zadná stena priskrutkovaná z vnútornej strany
Materiál	Skriňa, dizajnové dvere, zadná stena: ocelový plech
Povrch	Skriňa: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	Dekoratívne kryty: RAL 7015
Rozsah dodávky	Skriňa po stranách uzavretá Podlahové plechy, trojdielne Nivelačné nohy Dizajnové dvere, zadná stena priskrutkovaná z vnútornej strany
Rozmery	Šírka: 600 mm Výška: 900 mm Hĺbka: 600 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55
Balenie	1 pc(s).
Netto hmotnosť	44,6 kg
Brutto hmotnosť	46,6 kg

Features

PCF per pack (cradle-to-gate)	177,5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC002502
ETIM 8	EC002502
ECLASS 8.0	27180501
Popis výrobku	IW Industrial Workstation, skriňa, ŠxVxH: 600x900x600 mm, s dizajnovými dverami vpredu, zadná stena

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity