


**Rittal – The System.**

Faster – better – everywhere.



**DK 7000.625**

**Prístrojová polica, výsuvná**

State: 21.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7000.625 - Prístrojová polica, výsuvná pre TE

The complete set contains a vented component shelf, telescopic slides and a mounting kit for direct attachment, depth-variable attachment is possible, load capacity: 50 kg.

## Features

Obj. č.	DK 7000.625
Výhody	Hĺbkovo variabilný pre úpravu na vzdialenosť rovín 19" v rastrí 25 mm Plné vysunutie
Materiál	Dno: ocel'ový plech
Povrch	Podlaha: s nástrekom Montážna súprava/teleskopické lišty: pozinkované
Farba	RAL 7035
Rozsah dodávky	Prístrojová polica, s ventilačnými otvormi Teleskopické lišty s montážnou sadou
Load capacity static	500 N
Kontaktná plocha	Šírka: 409 mm Hĺbka: 500 mm
Rozmery	Šírka: 482,6 mm Hĺbka: 500 mm
Vzdialenosť medzi rovinami	395 - 645 mm
Balenie	1 pc(s).
Netto hmotnosť	4,577 kg
Brutto hmotnosť	4,777 kg
Číslo colnej sadzby	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261

# Features

---

Popis výrobku

DK Component shelf, WxD: 482,6x500 mm, 50 kg, distance between levels: 495 mm, depth-variable, For 482.6 mm (19") system punchings, RAL 7035