


# Rittal – The System.

Faster – better – everywhere.



## DK 7000.630

## Zásuvková lišta plastová

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7000.630 - Zásuvková lišta plastová

Socket strips 230 V, unrestricted use, including angular connectors, thanks to the long row arrangement of plug-type contacts.



## Features

Obj. č.	DK 7000.630
Materiál	Plast
Rozsah dodávky	Prívodný kábel Upevňovacie skrutky 2 vejárové podložky Klietkové matice M6, vodivé Matica
Prevedenie	Without switch
Zásuvky	8 x D, earthing-pin (type F, CEE 7/3)
Dĺžka prívodného kábla	2 m
Prívodný kábel (typ)	H05VV-F3G1.5 with wire end ferrules
Menovité prevádzkové napätie	230 V AC, 50 Hz
Menovité napätie	230 V AC, 50 Hz
Menovitý prúd (max.)	16 A
Spôsob (elektrického) pripojenia	Wire end ferrules
Možnosti montáže	TE 7000, rear 482.6 mm (19") section (> 2 U) TE 7000, vertically mounted on the frame

## Features

Farba telesa zásuvky	Čierna
Balenie	1 pc(s).
Netto hmotnosť	0,92 kg
Brutto hmotnosť	1,026 kg
Číslo colnej sadzby	85366990
ETIM 9	EC000330
ECLASS 8.0	27142604
Popis výrobku	Napájacia lišta DK-TS, pre montáž na rám skrine, vertikálne alebo do zadného profilu 482,6 mm (19"), Schuko (Typ F, CEE 7/3), 8-násobná, 230 V, 16 A

## Approvals

Explanations

Declaration of conformity