


Rittal – The System.

Faster – better – everywhere.



DK 7010.150 Senzory

State: 16.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7010.150 - Senzory for CMC III, PDU, LCP, IoT interface

The differential pressure sensor measures the air pressure at two points and displays the pressure difference between them.

Features

Obj. č.	DK 7010.150
Prevedenie	Differential pressure sensor
Výhody	Rýchle pripojenie a automatické rozpoznanie pomocou Plug & Play Napájanie elektrickou energiou sa vykonáva cez rozhranie CAN-Bus.
Oblasti použitia	Monitorovanie skríň v IT, priemysle a technickom zariadení budov. Monitorovanie skríň, miestností a kontajnerov v IT prostredí.
Popis funkcie	Settings can be made via the CMC III processing unit, PDU or IoT interface The differential pressure sensor measures the air pressure at two points in the room and displays the pressure difference between them. Dva body v priestore sa definujú pomocou tenkej hadice, ktorá sa pripojí k čidlu.
Materiál	Plast
Povrch	Čelná strana: hladká Skríňa: štruktúrovaná prášková farba
Farba	RAL 9005
Rozsah dodávky	Snímač Montážna doska Vrátane upevňovacieho materiálu
Pripojenie k zbernici CAN-Bus	Direct
Rozhranie	2 x RJ45 CAN bus
Rozmery	Šírka: 110 mm Výška: 30 mm Hĺbka: 40 mm
Rozsah prevádzkových teplôt	0 °C...45 °C

Features

Vlhkosť vzduchu (nekondenzujúca)	0...95 %
Balenie	1 pc(s).
Netto hmotnosť	0,333 kg
Brutto hmotnosť	0,383 kg
Číslo colnej sadzby	85319000
Popis výrobku	DK Differential pressure sensor, for bayed enclosure suites, connection via CAN bus interface, WxHxD: 110x30x40 mm, RAL 9005

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity