

# Rittal – The System.

Faster – better – everywhere.



## IT 7100.110 Rack OCP ORV3

State: 23.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 7100.110 - Rack OCP ORV3

Open. Efficient. Scalable. Your IT infrastructure from Rittal with OCP ORV3, without busbar. The Open Compute Project (OCP) brings together leading companies with the goal of making open IT infrastructures more efficient, scalable and sustainable. Rittal is supporting this vision with its OCP-compliant Open Rack Version 3 (ORV3), which is now also available without an integral busbar.



## Features

Obj. č.	IT 7100.110
Prevedenie	Otvorený rám without busbar
Výhody	Modulárny systém pre individuálne možnosti rozšírenia Flexible busbar selection, to suit the rack power density Can be retrofitted without replacing the entire system Modular configuration for AI and HPC applications Hot-pluggable components in the rack simplify maintenance work May be supplemented with a suitable direct liquid cooling solution Quick integration thanks to integral castor modules, air baffle plates and levelling feet Our range of accessories includes IT and power rails, 482.6 mm (19") adaptors, doors and side panels
Materiál	Oceľový plech
Povrch	Základná farba nanosená máčaním, na vonkajšej strane štruktúrovaná prášková farba
Farba	RAL 9005

# Features

Rozsah dodávky	Rack OCP ORV3 2 vzpery, predmontované Predinštalované kolieska pre vysoké zaťaženie Nivelačné nožičky, vopred zmontované Radové tesnenie
Rozmery	Šírka: 600 mm Výška: 2.286 mm Hĺbka: 1.068 mm
Výškové moduly	44 OU
Zaťažiteľnosť	14 000 N
Základný materiál	Sheet steel
Balenie	1 pc(s).
Číslo colnej sadzby	94032080
ETIM 8	EC002499
ECLASS 8.0	27180207
Popis výrobku	OCP ORV3 rack without busbar, 44 OU, WHD: 600 x 2286 x 1068 mm, RAL 9005