

Rittal – The System.

Faster – better – everywhere.



DK 7480.035

Energy-Box, 482,6 mm (19")

State: 22.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7480.035 - Energy-Box, 482,6 mm (19")

Depth-variable top hat rail for installed equipment to DIN 43 880, sizes 1 – 3 , maximum accommodation of 22 items of installed equipment.

Features

Obj. č.	DK 7480.035
Farba	RAL 7035
Rozsah dodávky	Energetický box s hĺbkovo nastaviteľnou DIN lištou pre inštalačné vstavané prístroje podľa DIN 43880, konštrukčná veľkosť 1–3, na zadnej strane s kefovou lištou na zavedenie kábla Plastový kryt vrátane zakrytia prázdneho poľa (UL 94-V0) 44 pripojovacích svoriek, 4 mm ² 2 pripojovacie svorky, 16 mm ² 2 zaslepovacie kryty 12 radových príchytiek na odľahčenie ťahu pri pripojovacích kábloch Označovacie pásky, samolepiace
Max. počet deliacich jednotiek @ 18 mm	22
Poznámka	Na vyžiadanie samostatné ističe namontované vo výrobe.
Rozmery	Šírka: 482,6 mm Výška: 132,5 mm Hĺbka: 155 mm
Výškové moduly	3 U
Balenie	1 pc(s).
Netto hmotnosť	2,354 kg
Brutto hmotnosť	2,54 kg
Číslo colnej sadzby	85366990
ETIM 9	EC002620
ECLASS 8.0	27189261
Popis výrobku	DK Energy-Box, na umiestnenie vstavaných zariadení, max. kapacita 22 TE, ŠxH: 482,6 (19") x 155 mm, 3 U, RAL 7035.