


Rittal – The System.

Faster – better – everywhere.



DK 7492.070

Klzné lišty, pre vysoké zaťaženie

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7492.070 - Klzné lišty, pre vysoké zaťaženie pre skrine pre dátové siete TS s dvoma upevňovacími rovinami

For TS network enclosures with two 482.6 mm (19") mounting levels, to support heavy installed equipment.

Features

Obj. č.	DK 7492.070
Prevedenie	Pre pevnú montáž medzi dve montážne roviny 19"
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho materiálu
Distance between mounting levels	698 mm
Zaťažiteľnosť	80 kg, statická záťaž
Poznámka	Nedá sa použiť v spojení s montážnym rámom 19" Vyberte prosím klznú lištu podľa príslušnej vzdialenosti medzi 19" rovinami. Pre kombináciu s profilovými lištami v tvare L je nutné použitie montážneho adaptéra pre profilové lišty v tvare L.
Kontaktná plocha	Šírka: 55 mm Hĺbka: 661 mm
Balenie	2 pc(s).
Netto hmotnosť	1,52 kg
Brutto hmotnosť	1,719 kg
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Popis výrobku	DK klzná lišta, pre dve montážne roviny 482,6 mm (19"), pre vysoké zaťaženie, 800 N, nosná plocha ŠxH: 55x661 mm