

# Rittal – The System.

Faster – better – everywhere.



## DK 7507.110 FlatBox

State: 4.7.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7507.110 - FlatBox

Flat-packed enclosure. For optimum access and flexible use as a wall-mounted or floor-standing enclosure.



## Features

Obj. č.	DK 7507.110
Prevedenie	s 19" profilovými lištami
Výhody	Rýchla montáž bez náradia Systémové príslušenstvo na otvorenej 19" konštrukcii
Materiál	Oceľový plech Sklenené okno: jednovrstvové bezpečnostné sklo, 3 mm
Povrch	Štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skriňa v prevedení Flat-Pack 1 nástenný diel 2 základné nosníky 2 strešné/podlahové plechy, s výrezmi na zavedenie káblov s kefovými lištami 2 bočnice, s možnosťou uzamknutia 1 presklené dvere s možnosťou uzamknutia, bezpečnostný zámok 3524 E, umiestnenie pántov voliteľné Spojovacie prvky pre rýchlu montáž bez náradia Uzemňovacia sada pre systémové uzemnenie všetkých súčastí skrinky 19" profilové lišty

## Features

Výškové moduly	9 U
Rozměry	Šířka: 600 mm Výška: 492 mm Hĺbka: 600 mm
Montážna výška pre komponenty	9 U
Zaťažiteľnosť	max. 450 N
Poznámka	Max. montážna hĺbka: Hĺbka - 58 mm až k zadnej stene Max. vzdialenosť medzi dvoma 19" rovinami: Hĺbka - 104 mm Uhol otvorenia dverí je max. 210°
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	24,42 kg
Brutto hmotnosť	26,3 kg
PCF per pack (cradle-to-gate)	102,9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC002500
ETIM 8	EC002500
ECLASS 8.0	27180208
Popis výrobku	DK FlatBox, nástenné/volne stojace skrine v balení FlatPack, s profilovými lištami 482,6 mm (19"), 9 U, ŠxVxH: 600 x 492 x 600 mm, 9 U

## Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------