


# Rittal – The System.

Faster – better – everywhere.



## DK 7688.000 19" profilové lišty

State: 7.7.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7688.000 - 19" profilové lišty pre skrine DK PS, CS New Basic

For mounting 482.6 mm (19") components in Networking and Server Racks DK PS and in Outdoor enclosures CS New Basic

## Features

Obj. č.	DK 7688.000
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho príslušenstva
Výškové moduly	24 U
Montážne rozmery	Installation depth for components: 482,6 mm Montážna šírka pre komponenty: 19"
Vhodné pre	Typ skrine: CS basic enclosures DK PS Výška: = 1.200 mm
Balenie	2 pc(s).
Netto hmotnosť	2,494 kg
Brutto hmotnosť	2,693 kg
PCF per pack (cradle-to-gate)	10,3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Popis výrobku	DK 19" profilové lišty, 24 U, pre V: 1200 mm