

Rittal – The System.

Faster – better – everywhere.



DK 7827.140

Profilové lišty, 482,6 mm (19")

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.140 - Profilové lišty, 482,6 mm (19") pre TS, CS Toptec

Mounting angles in cranked design Mounting angles are available in an L-shape as an alternative.

Features

Obj. č.	DK 7827.140
Prevedenie	Zalomené
Výhody	Značky U integrované v prednej strane uľahčujú systematickú montáž vo vnútri palcovej roviny
Technické údaje	Integrované 482,6 mm (19") otvory (norma EIA) Bočné okrúhle a štvorcové dierovanie Chromátované až k vodivému spoju 482.6 mm (19") vstavaných komponentov
Materiál	Oceľový plech, 2 mm
Rozsah dodávky	Vrátane upevňovacieho materiálu
Rozmery	Šírka: 482,6 mm
Výškové moduly	29 U
Poznámka	S profilovými lištami je možné realizovať aj upevňovacie rozmery 21", 23" a 24". Vyberte prosím klznú lištu podľa príslušnej vzdialenosti medzi 19" rovinami. Pre kombináciu s profilovými lištami v tvare L je nutné použitie montážneho adaptéra pre profilové lišty v tvare L.
Vhodné pre	Typ skrine: TS 8 CS Toptec Výška: 1.400 mm
Balenie	2 pc(s).
Netto hmotnosť	4,17 kg
Brutto hmotnosť	4,34 kg
Číslo colnej sadzby	73269098

Features

ETIM 9	EC002620
ECLASS 8.0	27189261
Popis výrobku	Profilová lišta DK-TS, 482,6 mm (19"), pre výšku skrine: 1400 mm, oceľový plech, odsadenie
