

Rittal – The System.

Faster – better – everywhere.



DK 7827.181

Profilové lišty, 482,6 mm (19")

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.181 - Profilové lišty, 482,6 mm (19") pre TS

L-shaped mounting angles, also for accommodating server system installation kits.

Features

Obj. č.	DK 7827.181
Prevedenie	Uholník tvaru L
Výhody	Značky U integrované v prednej strane uľahčujú systematickú montáž vo vnútri palcovej roviny Na profilové lišty v tvare L je možné upínať montážne sady serverových systémov Vhodné pre 19" vybavenie
Technické údaje	Integrované 482,6 mm (19") otvory (norma EIA) Bočné okrúhle a štvorcové dierovanie Chromátované až k vodivému spoju 482.6 mm (19") vstavaných komponentov
Materiál	Oceľový plech, 2 mm
Rozsah dodávky	Vrátane upevňovacieho materiálu
Výškové moduly	38 U
Poznámka	Vyberte prosím klznú lištu podľa príslušnej vzdialenosti medzi 19" rovinami. Pre kombináciu s profilovými lištami v tvare L je nutné použitie montážneho adaptéra pre profilové lišty v tvare L.
Vhodné pre	Typ skrine: TS Výška: 1.800 mm
Balenie	2 pc(s).
Netto hmotnosť	4,122 kg
Brutto hmotnosť	4,3 kg
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261

Features

Popis výrobku

DK-TS Mounting angles, 482.6 mm (19"), L-shaped mounting angle,
For H: 1800 mm, 38 U