


Rittal – The System.

Faster – better – everywhere.



DK 7859.080

PMS Zero-U

State: 4.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7859.080 - PMS Zero-U

Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.



Features

Obj. č.	DK 7859.080
Materiál	Hliníkový profil, eloxovaný v prírodnom farebnom odtieni
Dĺžka	1 695 mm
Spôsob (elektrického) pripojenia	Wago jack X-COM
Počet	2
Fáza pre každé napájanie	3~
Menovitý prúd (max.)	16 A
Počet slotov modulu (max.)	6
Stupeň krytia IP podľa normy IEC 60 529	IP 20
Montážny pokyn	Rôzne prívodné káble, aj na jednofázové pripojenie
Rozmery	Dĺžka: 1.695 mm
Vhodné pre	Typ skrine: VX IT Výška: ≥ 2.000 mm
Rozsah prevádzkových teplôt	5 °C...45 °C
Vlhkosť vzduchu (nekondenzujúca)	10...90 %

Features

Balenie	1 pc(s).
Netto hmotnosť	2,5 kg
Brutto hmotnosť	2,8 kg
Číslo colnej sadzby	85369001
ETIM 9	EC002762
ECLASS 8.0	27371306
Popis výrobku	DK Modular PDU, PSM prípojnice, modulárny rozvod energie pre vertikálnu montáž, v Zero-U pre IT rozvádzačov šírky 800 mm, 3~, 16 A, dĺžka: 1695 mm, sloty pre moduly: 6, prívody: 2, pripojenie: WAGO zásuvka, X-COM, pre výšku skrinky: 2000 mm, hliníkový profil, prírodný elox

Approvals

Explanations	Declaration of conformity
--------------	---------------------------