

Rittal – The System.

Faster – better – everywhere.



DK 7955.135

PDU, medzinárodné, prevedenie basic

State: 21.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7955.135 - PDU, medzinárodné, prevedenie basic

IT rack power distribution in a range of different variants. Input with CEE connector (16 A/32 A) and C13 and C19 outputs. Distribution output from 3.7 kW to 22 kW.

Features

| | |
|----------------------------------|--|
| Obj. č. | DK 7955.135 |
| Prevedenie | PDU Basic |
| Materiál | Hliníkový profil, čierno eloxovaný |
| Rozmery | Šírka: 44 mm Hĺbka: 62 mm Dĺžka: 1.405 mm |
| Počet zásuviek a typ | 42 x C13 |
| Zásuvky | 42 x IEC 320 socket C13 |
| Menovitý prúd (max.) | 16 A |
| Napájanie | Počet: 1 Fáza pre každé napájanie: 3~ |
| Dĺžka prívodného kábla | 3 m |
| Spôsob (elektrického) pripojenia | CEE |
| Smernica | Smernica EMC 2014/30/EÚ Smernica o nízkom napätí 2014/35/EU |
| Normy | EN 60950-1 |
| Rozsah prevádzkových teplôt | 0 °C...45 °C |
| Vlhkosť vzduchu (nekondenzujúca) | 10...95 % |
| Rozsah skladovacích teplôt | -25 °C...70 °C |
| Vhodné pre | Typ skrine: TS IT: ≥ 1.800 mm |
| Balenie | 1 pc(s). |
| Netto hmotnosť | 4,5 kg |
| Brutto hmotnosť | 4,7 kg |

Features

| | |
|---------------------|--|
| Číslo colnej sadzby | 85366990 |
| ECLASS 8.0 | 27142604 |
| Popis výrobku | DK PDU international, basic version, Compact basic power distributor, WLD: 44x1405x62 mm, 42xC13, black, CEE, 3~, 16 A |
