

# Rittal – The System.

Faster – better – everywhere.



## VX 8106.550

# Bočnice, na zoskrutkovanie, oceľový plech

State: 31.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8106.550 - Bočnice, na zoskrutkovanie, oceľový plech C4-H

Side panels, screw-fastened, sheet steel. Surface coating to DIN EN ISO 12944 corrosion protection class C4-H.

## Features

Obj. č.	VX 8106.550
Prevedenie	Povrchová úprava podľa DIN EN ISO 12944, trieda ochrany proti korózii C4-H Corrosion protection class C4-H
Materiál	Oceľový plech, 1,5 mm
Povrch	Štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Vrátane upevňovacieho materiálu
Vhodné pre	Typ skrine: VX C4-H Výška: = 2.000 mm Hĺbka: = 600 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55
Type rating podľa UL 50E	Type 1 Type 12
Základný materiál	Sheet steel
Balenie	2 pc(s).
Netto hmotnosť	26 kg
Brutto hmotnosť	29 kg
Číslo colnej sadzby	94039910
ETIM 9	EC002524
ETIM 8	EC002524
ECLASS 8.0	27182101

# Features

---

Popis výrobku

Bočnica VX, na zoskrutkovanie, pre VxH: 2000x600 mm, oceľový plech, C4-H