


Rittal – The System.

Faster – better – everywhere.



TS 8405.510

Systemy radových skříň TS 8

State: 25.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8405.510 - Systémy radových skříň TS 8

The TS 8 sheet steel baying system, with its symmetrical profile in the width and depth, offers a significant space gain, plus simple interior installation. This likewise ensures bayability from all sides. Additionally, the integral, automatic potential equalisation of all enclosure panels and the triple surface treatment ensure optimum safety.



Features

Obj. č.	TS 8405.510
Materiál	Rámová konštrukcia skrine: ocelový plech, 1,5 mm Strecha: ocelový plech 1,5 mm Dvere: ocelový plech, 2,0 mm Zadná stena: ocelový plech, 1,5 mm
Povrch	Rámová konštrukcia skrine: základná farba nanosená máčaním Dvere, strecha a zadná stena: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Rámová konštrukcia skrine Dvere U jednokrídlových skříň pánty dverí vpravo, možno zameniť na ľavú stranu Strešný plech Zadná stena 4 transportné oká Uzáver: Doppelbart, 3 mm
Rozmery	Šírka: 400 mm Výška: 2.000 mm Hĺbka: 500 mm

Features

Stupeň krytia IP podľa normy EN 60 529	IP 55 in conjunction with side panels and gland plates
Stupeň krytia NEMA	NEMA 12 in conjunction with side panels and gland plates
Type rating podľa UL 50E	Type 1 Type 12
Kód IK	IK09
Počet dverí	1
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	48,8 kg
Brutto hmotnosť	52 kg
Číslo colnej sadzby	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Popis výrobku	TS Bayed enclosure system, WHD: 400x2000x500 mm, sheet steel, without mounting plate, single door at the front

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK