

# Rittal – The System.

Faster – better – everywhere.



## TS 8602.400

## Diely podstavca predné a zadné, 200 mm

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8602.400 - Diely podstavca predné a zadné, 200 mm

## Oceľový plech, pre TS, TS IT, SE, CM, TP, PC, IW, TE

Base/plinth component consisting of one trim panel and two pre-configured corner pieces. In 200 mm high base/plinth components, one trim panel is divided into two for cable entry.

### Features

Obj. č.	TS 8602.400
Prevedenie	plná
Materiál	Diely podstavca: oceľový plech Krytky: plast
Povrch	S nástrekom
Farba	RAL 7022 Krytky: RAL 9005
Rozsah dodávky	2 diely podstavca 4 krytky Vrátane upevňovacieho materiálu
Rozmery	Výška: 200 mm
Vhodné pre	Typ skrine: TS: = 400 mm Typ skrine: SE Typ skrine: CM Typ skrine: TP Typ skrine: PC Typ skrine: IW Typ skrine: TS IT
Balenie	2 pc(s).
Netto hmotnosť	4,54 kg
Brutto hmotnosť	5,622 kg
Číslo colnej sadzby	94039910
ECLASS 8.0	27182003

# Features

---

Popis výrobku

TS Base/plinth component, front and rear, H: 200 mm, for W: 400 mm, RAL 7022, sheet steel