

Rittal – The System.

Faster – better – everywhere.



VX 8609.220 Kryt s dverami

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8609.220 - Kryt s dverami pre VX

Cover with door to protect and finish off connectors or other installed equipment

Features

Obj. č.	VX 8609.220
Výhody	Na ochranu a zakrytie konektorov alebo iných vstavaných súčastí Voliteľne zavedenie káblov zhora alebo zdola
Materiál	Kryt: ocelový plech, 1,5 mm Dvere: ocelový plech, 2,0 mm
Povrch	Základná farba nanosená máčaním, na vonkajšej strane štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Sklopný kryt Dvere s tyčovým uzáverom a s uzatváracou vložkou typu Doppelbart 2 krycie dosky, horné a dolné
Rozmery	Šírka: 202,7 mm Výška: 1.998 mm Hĺbka: 499 mm
Vhodné pre	Typ skrine: VX Výška: = 2.000 mm Hĺbka: = 500 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55 in conjunction with enclosures from the VX series
Stupeň krytia NEMA	NEMA 12 (in conjunction with enclosures from the VX, VX IT series)
Balenie	1 pc(s).
Netto hmotnosť	44 kg
Brutto hmotnosť	45 kg
PCF per pack (cradle-to-gate)	114,1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Features

Číslo colnej sadzby	94039910
ETIM 9	EC000744
ECLASS 8.0	27182405
Popis výrobku	VX kryt s dverami, pre VxH: 2000x500 mm
