


# Rittal – The System.

Faster – better – everywhere.



## VX 8618.210

## Komfortná rukoväť VX

State: 10.7.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8618.210 - Komfortná rukoväť VX pre VX, VX IT

Thanks to its folding action, the handle does not take up any swing space, thus maximising the door surface area available for installed equipment. Simple assembly, thanks to the snap-mounted handle system.



## Features

|                          |  |
|--------------------------|--|
| Obj. č.                  | VX 8618.210  |
| Prevedenie               | pripravené pre uzatvárací systém KESO/KABA   |
| Výhody                   | Vzhľadom na to, že vďaka technickému riešeniu nevyžaduje rukoväť so sklápaním žiadny priestor na otáčanie, je možné plochu dverí optimálne využiť na vstavanú montáž vybavenia<br>Jednoduchá montáž vďaka systému uchytenia rukoväte nacvaknutím |
| Materiál                 | Zinkový tlakový odliatok   |
| Farba                    | RAL 7035   |
| Uzáver                   | Vykonanie uzáveru: Pripravené pre KESO/KABA profilovú cylindrickú polvločku až do celkovej dĺžky 42,5 mm a Ø 22 mm   |
| Vhodné pre typ skrine    | VX<br>VX IT  |
| Type rating podľa UL 50E | Type 1<br>Type 3<br>Type 3R<br>Type 4<br>Type 12   |
| Balenie                  | 1 pc(s).   |
| Netto hmotnosť           | 0,6 kg   |

# Features

---

|                     |                                    |
|---------------------|------------------------------------|
| Brutto hmotnosť     | 0,72 kg                            |
| Číslo colnej sadzby | 83024110                           |
| ETIM 9              | EC000327                           |
| ECLASS 8.0          | 27409217                           |
| Popis výrobku       | Komfortná rukoväť VX pre Keso Kaba |

# Approvals

---

|           |  |
|-----------|--|
| Approvals | UL + C-UL (listed)<br>UL + C-UL - FTFA |
|-----------|--|