



Rittal – The System.

Faster – better – everywhere.



VX 8620.095

Bočnice podstavca s kefovou lištou

State: 21.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.095 - Bočnice podstavca s kefovou lištou pre systém podstavca VX

The 100 mm high base/plinth trim panels are used in the width or depth for cable entry into the base/plinth. The trim panels may also be used in a 200 mm high base/plinth and combined with other 100 mm high trim panels.

Features

Obj. č.	VX 8620.095
Materiál	Bočnice podstavca: ocelový plech Kefová lišta: plast, samozhášacia
Farba	RAL 9005
Rozsah dodávky	Vrátane upevňovacieho materiálu
Rozmery	Výška: 100 mm
Vhodné pre	Šírka/hĺbka: 1.200 mm
Type rating podľa UL 50E	Type 1, 12
Hmotnosť/balenie	2,8 kg
Balenie	2 pc(s).
Netto hmotnosť	2,5 kg
Brutto hmotnosť	2,8 kg
Číslo colnej sadzby	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003
Popis výrobku	VX Base/plinth trim panel, with brush strip, for W/D: 1200 mm

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------