


Rittal – The System.

Faster – better – everywhere.



VX 8640.044

Bočnice podstavca, 200 mm

State: 13.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8640.044 - Bočnice podstavca, 200 mm pre systém podstavca VX, ocelový plech

To finish off a base/plinth unit at the sides and for additional stability or interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

Features

Obj. č.	VX 8640.044
Materiál	Ocelový plech
Farba	RAL 9005
Rozsah dodávky	Vrátane upevňovacieho materiálu
Rozmery	Výška: 200 mm
Vhodné pre	Hĺbka: = 800 mm
Type rating podľa UL 50E	Type 1 Type 12
Hmotnosť/balenie	4,14 kg
Balenie	2 pc(s).
Netto hmotnosť	3,94 kg
Brutto hmotnosť	4,14 kg
Číslo colnej sadzby	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003
Popis výrobku	VX Base/plinth trim panel, side, H: 200 mm, for D: 800 mm, sheet steel

Approvals

Approvals

Approvals

UL + C-UL - FTTA