


Rittal – The System.

Faster – better – everywhere.



VX 8660.046 Bočnice podstavca

State: 17.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.046 - Bočnice podstavca pre systém podstavca VX, ocel'ový plech

To finish off a base/plinth unit at the sides and for additional stability or interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.



Features

Obj. č.	VX 8660.046
Prevedenie	Uzavreté
Materiál	Ocel'ový plech
Farba	RAL 9005
Rozsah dodávky	Vrátane upevňovacieho materiálu
Rozmery	Výška: 200 mm
Vhodné pre	Typ skrine: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Hĺbka: = 1.200 mm

Features

Type rating podľa UL 50E	Type 1 Type 12
Hmotnosť/balenie	7,12 kg
Balenie	2 pc(s).
Vhodné pre	pre systém podstavca VX, oceľový plech
Netto hmotnosť	7,12 kg
Brutto hmotnosť	7,124 kg
PCF per pack (cradle-to-gate)	21,83 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Popis výrobku	VX kryt podstavca, bočný, V: 200 mm, pre H: 1200 mm, oceľový plech

Approvals

Explanations	PCF-declaration
--------------	-----------------