


Rittal – The System.

Faster – better – everywhere.



VX 8660.095

Bočnice podstavca s kefovou lištou

State: 11.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.095 - Bočnice podstavca s kefovou lištou pre systém podstavca VX, ocelový plech

For cable entry in the base/plinth. With a 200 mm base/plinth height, one or two trim panels with brush strip may optionally be used. Thanks to the optional trim panel attachment, the trim panels with brush strip may also be fitted at the front, rear or side of the base/plinth corner piece.

Features

Obj. č.	VX 8660.095
Prevedenie	s kefovou lištou
Materiál	Bočnice podstavca: ocelový plech Kefová lišta: plast, samozhášacia
Farba	RAL 9005
Rozmery	Výška: 100 mm
Vhodné pre	Typ skrine: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Šírka/hĺbka: 1.200 mm
Balenie	2 pc(s).
Vhodné pre	pre systém podstavca VX, ocelový plech
Montážny pokyn	Pre inštaláciu do hĺbky je potrebné zvoliť opciiu upevnenia krytu
Netto hmotnosť	2,5 kg
Brutto hmotnosť	2,554 kg
Číslo colnej sadzby	94039910
ETIM 9	EC000721

Features

ETIM 8	EC000721
ECLASS 8.0	27182003
Popis výrobku	Kryt podstavca VX s kefovou lištou, pre šírku/hĺbku: 1200 mm
