


Rittal – The System.

Faster – better – everywhere.



TS 8702.050

Bočnice podstavca, 200 mm

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8702.050 - Bočnice podstavca, 200 mm Z nerezovej ocele pre predné a zadné diely podstavca

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used.

Features

Obj. č.	TS 8702.050
Materiál	Nerezová oceľ 1.4301 (AISI 304)
Povrch	Jemne zbrúsený povrch, zrnitosť 400
Rozsah dodávky	2 bočnice podstavca Vrátane upevňovacieho materiálu
Montážny pokyn	Pre stabilizáciu dielov podstavcov prepojených v rade môžu byť bočnice podstavcov s výškou 100 mm namontované s pootočením o 90°. Vtedy sú nutné spojovacie diely pre radové prepojenie podstavca.
Rozmery	Výška: 200 mm
Vhodné pre	Typ skrine: TS: = 500 mm
Balenie	2 pc(s).
Netto hmotnosť	3,38 kg
Brutto hmotnosť	3,56 kg
Číslo colnej sadzby	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003
Popis výrobku	TS kryt podstavca, bočný, V: 200 mm, pre Š: 500 mm, nehrdzavejúca oceľ, 1.4301