

**Rittal – The System.**

Faster – better – everywhere.



# TS 8800.753 Káblový kanál

State: 21.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8800.753 - Káblový kanál

With special DIN punchings for direct mounting on the enclosure section or on surfaces such as mounting plates. Nominal break points on the bars and on the cable duct base.



## Features

Obj. č.	TS 8800.753
Prevedenie	pre montážne dosky pre montáž na VX systémové dierovanie
Materiál	Tvrdé PVC Nehorľavé, samozhášavé Teplotná odolnosť do +60 °C
Farba	V odtieni podobnom RAL 7030
Rozsah dodávky	Káblový kanál s vekom
Bar width	5,5 mm
Slot width	4,5 mm
Možnosti montáže	So špeciálnym dierovaním podľa DIN pre priamu montáž na profil skrine alebo plochy, napr. montážne dosky Pokiaľ je montážna doska vzadu namontovaná ako lícujúca s rámom rozvádzača (montážna pozícia $\pm 0$ mm), lícujú horizontálne namontované káblové kanály s káblovými kanálmi na profile skrine.
Poznámka	Je možné pre iné rozmery skrátiť.
Rozmery	Šírka: 80 mm Hĺbka: 80 mm Dĺžka: 2.000 mm
Balenie	12 pc(s).

# Features

---

Netto hmotnosť	17,88 kg
Brutto hmotnosť	18,72 kg
Číslo colnej sadzby	39259020
ETIM 9	EC000012
ECLASS 8.0	27400703
Popis výrobku	TS káblový kanál pre montážnu dosku, ŠxVxH: 80x2000x80 mm

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---