


Rittal – The System.

Faster – better – everywhere.



SV 9340.820

Zdvojené vodiče

State: 4.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.820 - Zdvojené vodiče pre OM adaptéry so svorkou s ťažnou pružinou 2,5 – 16 mm²

Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.



Features

Obj. č.	SV 9340.820
Materiál	Izolácia z PVC Teplotná odolnosť do 105 °C Konce vodičov na oboch stranách zlisované ultrazvukom
Prierez	AWG 10 = 5.26 mm ² × 6 mm ²
Poznámka	AWG = americké rozmery vodičov
Rozmery	Dĺžka: 140 mm, 250 mm
Balenie	6 pc(s).
Netto hmotnosť	0,138 kg
Brutto hmotnosť	0,16 kg
Podiel medi (kg / ks)	0,013
Číslo colnej sadzby	85444290
ETIM 9	EC000839
ECLASS 8.0	27400613
Popis výrobku	Dvojitý kábel SV, AWG 10, D1: 140 mm, D2: 250 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK