

Rittal – The System.

Faster – better – everywhere.



RX 9360.000 RiLineX baying set

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.000 - RiLineX baying set pre dosku

RiLineX baying connector set for the 3-pole complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed VX enclosures, no drilling required.



Features

Obj. č.	RX 9360.000
Výhody	Time savings thanks to fully digital product data Reduced assembly time thanks to pre-assembled complete board Tested short-circuit resistance up to 65 kA Suitable for applications up to 1000 V AC and up to 1500 V DC Tested and certified to IEC and UL Simple extension and baying
Materiál	Horná časť: oceľový plech, pozinkovaný Kontaktná doštička: E-Cu, pocínovaná Predný kryt: polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94
Farba	RAL 35745
Rozsah dodávky	3 spojky prípojnic 1 predný kryt 1 izolačný panel
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Normy	IEC 61 439-1/-2 UL 508

Features

Menovitý prúd max.	780 A
Menovitý prúd (UL)	780 A
Elektrické parametre UL (SCCR)	52.5 kA - 600 V, RMS, unprotected 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Menovité rázové napätie Uimp	12 kV
Rated voltage	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage Ui	1 000 V AC 1 500 V DC
Rated impulse withstand current	103 kA 115,5 kA
Rated short-term withstand current/t	45 kA/200 ms 52,5 kA/500 ms
Trieda prepätia	4
Stupeň znečistenia	3
Počet pólov	3-pole
Vhodný pre obj. č.	9360004 9360008 9360024 9360028 9360064 9360068 9360084 9360088
Frekvencia základného kmitania	50...60 Hz
Vlhkosť vzduchu (nekondenzujúca)	10...90 %
Vhodné pre prípojnice	30 x 5/10
Rozsah prevádzkových teplôt	-5 °C...55 °C

Features

Rozmery	Šírka: 154 mm Výška: 240 mm Hĺbka: 77 mm
Balenie	1 pc(s).
Netto hmotnosť	1,88 kg
Brutto hmotnosť	1,924 kg
Podiel medi (kg / ks)	0,297
PCF per pack (cradle-to-gate)	10,32
Číslo colnej sadzby	85369010
ETIM 9	EC002270
Popis výrobku	RiLineX baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple, no-drill baying of boards between two bayed enclosures. Baying connectors are included with the supply.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration