

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.500

## RiLineX CB component adaptor

State: 19.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.500 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



## Features

Obj. č.	RX 9360.500
Prevedenie	Easy Fix
Výhody	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94
Farba	RAL 9005 RAL 35745
Rozsah dodávky	3 connection space covers
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Menovité rázové napätie Uimp	8 kV

# Features

Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage $U_i$	1 000 V
Rated impulse withstand current	80 kA
Stupeň znečistenia	3
Počet pólov	3-pole
Vývod vodičov	Bottom
Spôsob (elektrického) pripojenia	Box terminal
Vhodné pre výrobcov (typ)	ABB (A1, S2, T1, T2, XT1, XT2, FD63/FD160) BTicino (M1 160) Chint (NM8N-125, NM1-63H, NM1-125H, NXM-63S, NXM-125S, NXM-160S, NXMS-160) Eaton (NZM1) Fuji Electric (BW125JAG-3P) Hager (P160) Himel (HDM3-100F/N, HDM3L-125) Hyundai Electric (100AF, 125AF, 125D, 160D AF) Legrand (DPX 160, DPX 250 ER, DPX <sup>3</sup> 160) LS Electric (100AF, 125AF, TE100, TD100, TE160, TD160) Mitsubishi (NF63-SV, NF125-SV) OEZ (BC160) Rockwell (140G-C2C3-D10, 140G-C2C3-D12, 140-C2E3-D16, 140G-H0F3-D10, 140G-H0F3-D12, 140G-H0F3-D16) Sassin (3SM8L-100) Schneider (NSC100N, NSXm50, NSXm100, NSXm160, NSXm250, NSE100) Schrack (MC1) Siemens (3VA10, 3VA11) Terasaki (E125, S125)
Vhodné pre prípojnicový systém	RiLineX RiLine60
Frekvencia základného kmitania	50...60 Hz
Vlhkosť vzduchu (nekondenzujúca)	10...90 %

# Features

Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Rozsah prevádzkových teplôt	-25 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Rozmery	Šírka: 82 mm Výška: 252 mm Hĺbka: 63 mm
Balenie	1 pc(s).
Netto hmotnosť	1,364 kg
Brutto hmotnosť	1,367 kg
Podiel medi (kg / ks)	0,375
PCF per pack (cradle-to-gate)	13,28
Číslo colnej sadzby	85369095
ETIM 9	EC001531
Popis výrobku	RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration