

Rittal – The System.

Faster – better – everywhere.



RX 9360.512

RiLineX CB component adaptor

State: 27.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.512 - RiLineX CB component adaptor

This new product is currently unavailable. Alternatively, you can use the item number 9360.612.



Features

| | |
|---|---|
| Obj. č. | RX 9360.512 |
| Prevedenie | Easy Fix |
| Výhody | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Materiál | Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94 |
| Farba | RAL 9005 RAL 35745 |
| Rozsah dodávky | 3 connection space covers |
| Stupeň krytia IP podľa normy IEC 60 529 | IP 2XB |
| Menovité rázové napätie Uimp | 8 kV |
| Rated voltage | 690 V AC 600 V AC (UL) |
| Rated insulation voltage Ui | 1 000 V |

Features

| | |
|---|--|
| Stupeň znečistenia | 3 |
| Priestor na upevnenie lamelových medených prípojnic (Š x V) | 15 x 6 mm |
| Počet pólov | 3-pole |
| Vývod vodičov | Bottom |
| Spôsob (elektrického) pripojenia | Screw M8 |
| Vhodné pre výrobcov (typ) | ABB (S3 150, S3 225, S3, T3, T4, XT3, XT4, FE160, FE250) Chint (NM8N-250, NM1-250H, NXM-250S, NXMS-250) Eaton (LZMB2-A160, LZMB2-A250) Fuji Electric (BW160_-3P, BW250_-3) Hager (P250) Himel (HDM3-160, HDM3-250, HDM3L-160, HDM3L-250) Hyundai Electric (160, 250AF) Legrand (DPX250, DPX ³ 250) LS Electric (250AF, TS250) Mitsubishi (NF125-SGV, NF160-SGV, NF250-SV) OEZ (BD250) Rockwell (140G-J0F3-D25) Sassin (3SM8N-225, 3SM8L-225) Schneider (EZC250H, NS100, NS160, NS250, NSX100, NSX160, NSX250, GV5) Schrack (MC2) Siemens (3VA20, 3VA21, 3VA22, 3VT2, 3RV1063, 3RV1363, 3RV1364, VL160/3VL2) Terasaki (S160, S250, H250) |
| Vhodné pre prípojnicový systém | RiLineX RiLine60 |
| Frekvencia základného kmitania | 50...60 Hz |
| Vlhkosť vzduchu (nekondenzujúca) | 10...90 % |
| Vhodné pre prípojnice | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Rozsah prevádzkových teplôt | -25 °C...55 °C |
| Rozsah skladovacích teplôt | -25 °C...75 °C |

Features

| | |
|-------------------------------|---|
| Rozmery | Šírka: 105 mm Výška: 252 mm Hĺbka: 63 mm |
| Balenie | 1 pc(s). |
| Netto hmotnosť | 1,7 kg |
| Brutto hmotnosť | 1,792 kg |
| Podiel medi (kg / ks) | 0,608 |
| PCF per pack (cradle-to-gate) | 10,84 |
| Číslo colnej sadzby | 85369095 |
| ETIM 9 | EC001531 |
| Popis výrobku | RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom. |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity PCF-declaration |