

Rittal – The System.

Faster – better – everywhere.



RX 9360.612

RiLineX CB component adaptor

State: 7.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.612 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Features

Obj. č.	RX 9360.612
Prevedenie	univerzálna
Výhody	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94
Farba	RAL 9005 RAL 35745
Rozsah dodávky	3 connection space covers
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Menovité rázové napätie Uimp	8 kV

Features

Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage Ui	1 000 V
Stupeň znečistenia	3
Počet pólov	3-pole
Vývod vodičov	Bottom
Spôsob (elektrického) pripojenia	Screw M8
Prierez	15 mm ² 6 mm ²
Vhodné pre výrobcov (typ)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Vhodné pre prípojnicový systém	RiLineX RiLine60
Frekvencia základného kmitania	50...60 Hz
Vlhkosť vzduchu (nekondenzujúca)	10...90 %
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Rozsah prevádzkových teplôt	-25 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Rozmery	Šírka: 109 mm Výška: 251,4 mm Hĺbka: 62,8 mm
Fire load	8,086 MJ/m ²
Balenie	1 pc(s).
Netto hmotnosť	1,472 kg
Brutto hmotnosť	1,474 kg
Podiel medi (kg / ks)	0,608
PCF per pack (cradle-to-gate)	9,96
Číslo colnej sadzby	85369095

Features

ETIM 9	EC001531
Popis výrobku	RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration