

Rittal – The System.

Faster – better – everywhere.



RX 9360.612

RiLineX CB component adaptor

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.612 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Features

| | |
|---|---|
| Obj. č. | RX 9360.612 |
| Prevedenie | univerzálna |
| Výhody | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Materiál | Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94 |
| Farba | RAL 9005 RAL 35745 |
| Rozsah dodávky | 3 connection space covers |
| Stupeň krytia IP podľa normy IEC 60 529 | IP 2XB |
| Menovité rázové napätie Uimp | 8 kV |

Features

| | |
|----------------------------------|---|
| Rated voltage | 690 V AC 600 V AC (UL) |
| Rated insulation voltage Ui | 1 000 V |
| Stupeň znečistenia | 3 |
| Počet pólov | 3-pole |
| Vývod vodičov | Bottom |
| Prierez | 15 mm ² 6 mm ² |
| Vhodné pre výrobcov (typ) | Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor. |
| Vhodné pre prípojnicový systém | RiLineX RiLine60 |
| Frekvencia základného kmitania | 50...60 Hz |
| Vlhkosť vzduchu (nekondenzujúca) | 10...90 % |
| Vhodné pre prípojnice | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Rozsah prevádzkových teplôt | -25 °C...55 °C |
| Rozsah skladovacích teplôt | -25 °C...75 °C |
| Rozmery | Šírka: 108,7 mm Výška: 251,4 mm Hĺbka: 62,8 mm |
| Balenie | 1 pc(s). |
| Netto hmotnosť | 1,472 kg |
| Brutto hmotnosť | 1,474 kg |
| Podiel medi (kg / ks) | 0,608 |
| PCF per pack (cradle-to-gate) | 9,96 |
| Číslo colnej sadzby | 85369095 |
| ETIM 9 | EC001531 |

Features

Popis výrobku

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom.

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity
PCF-declaration