

Rittal – The System.

Faster – better – everywhere.



RX 9360.730

RiLineX component adaptor

State: 21.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.730 - RiLineX component adaptor

RiLineX component adaptor (32 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



Features

Obj. č.	RX 9360.730
Prevedenie	s prírodným káblom
Výhody	For mounting equipment for top hat rail installation, e.g. motor starter Pre-assembled connection cable Simple clip locking for support rails Optional anti-slip guard Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Jednoduchá montáž Coordinated accessories reduce the number of different items required
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94
Farba	RAL 9005 RAL 35745
Pripojovacie vodiče (AWG)	AWG 10
Menovitý prúd (max.)	40 A

Features

Rated current of round conductor	40 A
Rated current of round conductor (UL)	40 A
Vývod vodičov	Bottom
Pre prípojnicové systémy s rozstupom	60 mm
Dĺžka prívodného kábla	160 mm
Počet pólov	3-pole
Vhodné pre prípojnicový systém	RiLineX RiLine60
Rozmery	Šírka: 45 mm Výška: 239,4 mm Hĺbka: 36,2 mm
Počet nosných líšt / výška	1 / 10 mm
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Stupeň znečistenia	3
Normy	IEC 61 439-1/-2 UL 508
Menovité rázové napätie Uimp	8 kV
Rated insulation voltage Ui	1 000 V
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Rozsah prevádzkových teplôt	-5 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Vlhkosť vzduchu (nekondenzujúca)	10...90 %

Features

Balenie	4 pc(s).
Netto hmotnosť	1,42 kg
Brutto hmotnosť	1,45 kg
Podiel medi (kg / ks)	0,088
PCF per pack (cradle-to-gate)	9,34
Číslo colnej sadzby	85369095
ETIM 9	EC001531
Popis výrobku	RiLineX component adaptor (32 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration