

Rittal – The System.

Faster – better – everywhere.



RX 9362.000

RiLineX NH fuse-switch
disconnecter

State: 25.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.000 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required.



Features

Obj. č.	RX 9362.000
Prevedenie	For 60 mm busbar systems
Výhody	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94 Kontaktové dráhy: elektrolytická meď, postriebrená
Farba	RAL 9005 RAL 35745
Pre prípojnicové systémy s rozstupom	60 mm
Vývod vodičov	Top/bottom

Features

Spôsob (elektrického) pripojenia	Screw M8
Poistkové vložky	NH 00 NH 000
Menovité prevádzkové napätie	690 V AC
Pre veľkosť NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (poistkové vložky)
Rozmery	Šírka: 106 mm Výška: 194,2 mm Hĺbka: 104,5 mm
Rozsah prevádzkových teplôt	-5 °C...35 °C
Rozsah skladovacích teplôt	-25 °C...70 °C
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Vhodné pre prípojnicový systém	RiLine60 RiLineX
Počet pólov	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Stupeň znečistenia	3
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Fire load	14,2 MJ/m ²
Stratový výkon max.	19 W
Heat loss per fuse insert (max.)	12 W
Balenie	1 pc(s).
Netto hmotnosť	1,015 kg
Brutto hmotnosť	1,023 kg

Features

Podiel medi (kg / ks)	0,363
PCF per pack (cradle-to-gate)	6,85
Číslo colnej sadzby	85369095
ETIM 9	EC001040
Popis výrobku	RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required.

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration