


Rittal – The System.

Faster – better – everywhere.



RX 9362.315

**RiLineX NH fuse-switch
disconnecter**

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.315 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



Features

Obj. č.	RX 9362.315
Prevedenie	For 60 mm busbar systems
Výhody	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work High rated voltage 800 V ready All variants also available with electronic fuse monitoring
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94 Kontaktové dráhy: elektrolytická meď, postriebrená
Farba	RAL 9005 RAL 35745
Rozsah dodávky	Connectors for electronic fuse monitoring
Pre prípojnicové systémy s rozstupom	60 mm
Vývod vodičov	Top/bottom
Spôsob (elektrického) pripojenia	Screw M10
Poistkové vložky	NH 3

Features

Menovité prevádzkové napätie	690 V AC
Pre veľkosť NH	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (poistkové vložky)
Rozmery	Šírka: 250 mm Výška: 348,6 mm Hĺbka: 134,9 mm
Rozsah prevádzkových teplôt	-5 °C...35 °C
Rozsah skladovacích teplôt	-25 °C...70 °C
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Vhodné pre prípojnicový systém	RiLineX RiLine60
Počet pólov	3-pole
Stupeň znečistenia	3
s elektronickou indikáciou stavu poistiek (ESÜ)	Yes
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Fire load	47,58 MJ/m ²
Stratový výkon max.	101 W
Balenie	1 pc(s).
Netto hmotnosť	4,7 kg
Brutto hmotnosť	4,83 kg
Podiel medi (kg / ks)	2,255
PCF per pack (cradle-to-gate)	32,08
Číslo colnej sadzby	85369095
ETIM 9	EC001040

Features

Popis výrobku

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.

Approvals

Approvals

CQC-CCC

Explanations

Declaration of conformity
PCF-declaration