

# Rittal – The System.

Faster – better – everywhere.



## RX 9363.005

# RiLineX NH fuse-switch disconnecter

State: 14.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9363.005 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Includes electronic fuse monitoring.



## Features

Obj. č.	RX 9363.005
Prevedenie	Na inštaláciu na montážnu dosku
Výhody	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94 Kontaktové dráhy: elektrolytická meď, postriebrená
Farba	RAL 9005 RAL 35745
Rozsah dodávky	Connectors for electronic fuse monitoring
for mounting plate assembly	Yes
Vývod vodičov	Top/bottom

# Features

Spôsob (elektrického) pripojenia	Screw M8
Poistkové vložky	NH 00 NH 000
Rated insulation voltage $U_i$	1 000 kV
Menovité prevádzkové napätie	690 V AC
Pre veľkosť NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (poistkové vložky)
Rozmery	Šírka: 106 mm Výška: 228,9 mm Hĺbka: 86,1 mm
Rozsah prevádzkových teplôt	-5 °C...35 °C
Rozsah skladovacích teplôt	-25 °C...70 °C
Počet pólov	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Stupeň znečistenia	3
s elektronickou indikáciou stavu poistiek (ESŮ)	Yes
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Fire load	13,24 MJ/m <sup>2</sup>
Stratový výkon max.	16 W
Heat loss per fuse insert (max.)	12 W
Balenie	1 pc(s).
Netto hmotnosť	0,82 kg
Brutto hmotnosť	0,917 kg
Podiel medi (kg / ks)	0,18

## Features

---

PCF per pack (cradle-to-gate)	5,51
Číslo colnej sadzby	85369095
ETIM 9	EC001040
Popis výrobku	RiLineX NH fuse-switch disconnecter in size 00 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M8 screw terminal connection. Includes electronic fuse monitoring.

## Approvals

---

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration